

Hydrogen Sulphide CiTiceL[®] Specification



4HS/LM CiTiceL[®]

(Standard version)

Performance Characteristics


Nominal Range	0-100ppm
Maximum Overload	500ppm
Expected Operating Life	Two years in air
Output Signal	0.70 ± 0.15 µA/ppm
Resolution	0.1ppm
Temperature Range	-40°C to +50°C
Pressure Range	Atmospheric ± 10%
Pressure Coefficient	No data
T₉₀ Response Time	≤30 seconds
Relative Humidity Range	15 to 90% non-condensing
Typical Baseline Range (pure air)	-0.1 to +0.4ppm equivalent
Maximum Zero Shift (+20°C to +40°C)	<0.2ppm equivalent
Long Term Output Drift	<2% signal loss/month
Recommended Load Resistor	10Ω
Bias Voltage	Not required
Repeatability	<2% of signal
Output Linearity	Linear

N.B. All performance data is based on conditions at 20°C, 50%RH, and 1013mBar

Physical Characteristics

Weight	5g (approx.)
Position Sensitivity	None
Storage Life	Six months in CTL container
Recommended Storage Temperature	0-20°C
Warranty Period	12 months from date of despatch

Outline Dimensions



All dimensions in mm
All tolerances ±0.15mm unless otherwise stated


IMPORTANT NOTE: Connection should be made via PCB sockets only. Soldering to the pins will seriously damage your sensor.

Testing: 4HS/LM Hydrogen Sulphide CiTiceLs should be tested monthly to confirm sensitivity and response time are adequate.


Hydrogen Sulphide CiTiceL[®] Specification



4HS Hydrogen Sulphide CiTiceL - Output vs Temperature



4HS Hydrogen Sulphide CiTiceL - Baseline vs Temperature



Cross-sensitivity Data

CiTiceLs may exhibit a response to certain gases in a sample other than the target gas. 4HS/LM CiTiceLs have been tested with a number of commonly cross-interfering gases and the results are given below. The table shows the typical response to be expected from a sensor when exposed to a given test gas concentration (relevant to safety, e.g. TLV levels).

Gas	Conc.	4HS/LM	Gas	Conc.	4HS/LM
Carbon monoxide:	300ppm	≤2ppm	Hydrogen:	10000ppm	≤10ppm
Sulphur dioxide:	5ppm	≈1ppm	Nitrogen dioxide:	5ppm	≈-1ppm
Nitric oxide:	35ppm	<0.7ppm			

For details of other possible cross-interfering gases contact City Technology.

Methanol Sensitivity

The 4HS/LM CiTiceL is designed for use in applications where methanol might be present. Whilst cross sensitivity reactions on CiTiceLs are normally readily defined, the behavior of the 4HS/LM when exposed to methanol is significantly more complex, and can not be specified as above for carbon monoxide. The 4HS/LM CiTiceL is the result of an extensive development project, which has achieved, for this application, a significant performance advantage over standard 4HS CiTiceLs.

For more detailed information about the response to methanol please contact Technical Support at City Technology.

Every effort has been made to ensure the accuracy of this document at the time of printing. In accordance with the company's policy of continued product improvement City Technology Limited reserves the right to make product changes without notice. No liability is accepted for any consequential losses, injury or damage resulting from the use of this document or from any omissions or errors herein. The data is given for guidance only. It does not constitute a specification or an offer for sale. The products are always subject to a programme of improvement and testing which may result in some changes in the characteristics quoted. As the products may be used by the client in circumstances beyond the knowledge and control of City Technology Limited, we cannot give any warranty as to the relevance of these particulars to an application. It is the clients' responsibility to carry out the necessary tests to determine the usefulness of the products and to ensure their safety of operation in a particular application.

Performance characteristics on this data sheet outline the performance of newly supplied sensors. Output signal can drift below the lower limit over time.